

TECHNICAL DATA SHEET

NANO SILVER PLUS WB

Special additive with silver ions for water-based sealers



DESCRIPTION

NANO SILVER PLUS WB is a special silver ion-based additive for PU FEST 2K water-based sealer and PU FEST 2K CARBON. It creates a hygienic protective coating. It does not change the sealer's hardness. It does not affect gloss or viscosity. It maintains the sealer's mechanical and chemical resistance. Certified according to ISO 22196.

TECHNICAL DATA

- Color: colorless
- Application temperature: +15°C ÷ +25°C
- Light foot traffic is possible after 24 hours, full load after 7 days
- Open time: 1 hour
- Shelf life: 12 months in original sealed packaging, at a temperature of +10°C to +25°C

DIRECTIONS FOR USE

Shake thoroughly before use. Add NANO SILVER PLUS WB to PU FEST 2K at a ratio of 2% to the total of the components and the sealer. Mix thoroughly. Apply with a microfiber roller, just like the other sealers in the Festfloor line. It can be used with the 3K PLUS additive. It is not recommended to add more NANO SILVER PLUS WB than recommended.

- Add 120 g of NANO SILVER PLUS WB to PU FEST 2K sealer (5kg + 1kg).
- Add 25 g of NANO SILVER PLUS WB to PU FEST 2K sealer (1kg + 0,2kg).
- Add 120 g of NANO SILVER PLUS WB to PU FEST 2K CARBON sealer (5kg + 0,4kg).
- Add 25 g of NANO SILVER PLUS WB to PU FEST 2K CARBON sealer (1kg + 80g).

PACKAGING

- 120 g,
- 25 g.

SAFETY AND HEALTH

H318 – Causes serious eye damage. H317 – May cause an allergic skin reaction. H400 – Very toxic to aquatic life. H411 – Toxic to aquatic life with long-lasting effects. P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P280 Wear protective gloves/protective clothing/eye protection/face protection. P310 Immediately call a doctor. P273 Avoid release to the environment. P391 Collect spillage. Contains: 1-2-BENZISOTHAZOLINE 3 (2H)-ONE.